



Your Laundry & Infection Control Partner

JLA 33, 40, 50 and 65

Free-standing, High Speed Spin Washers



JLA 33

JLA 40

JLA 50

JLA 65

THE PROFESSIONALS CHOICE



Your Laundry & Infection Control Partner

SPECIFICATIONS

Details	Units	JLA 33	JLA 40	JLA 50	JLA 65
Capacity	Kg(lb)	14.5(33)	18(40)	23.4(50)	30.4(65)
Height	mm	1348	1348	1500	1530
Width	mm	780	780	900	1060
Depth	mm	841	941	1010	1147
Net Weight	Kg	363	391	534	731
Drum Volume	m ³ /l	0.145/145	0.18/185	0.234/234	0.304/304
G.Force	Gs	380	380	420	475
Door Opening	Ø mm	400	400	400	400
Electrics- 18KW Heater	Volt/ph/Amp	415/3/45	415/3/45	415/3/45	415/3/45
Electrics- Steam Heated	Volt/ph/Amp	240/1/16	240/1/16	240/1/16	415/3/16
No. of Water Connections	cold/hot	2/1	2/1	2/1	2/1
Size	"BSP	3/4	3/4	3/4	3/4
Drain Connection (Gravity)	Ø mm	50	50	75	75
Steam Rating	Kg(lb)/cycle	15(32)	18(40)	23.4(51)	30.4(67)
Size	"BSP	3/8	3/8	3/8	3/8

All specifications subject to change without notice

JLA 33, 40, 50 and 65

Free-standing, High Speed Spin Washers

Machines in this range are ideal for contamination risk sites such as hospitals, care homes, hotels, veterinary surgeries, laundries and dry cleaners. They meet NHS Guideline HSG (95)18, Category 5 of the latest Water Regulations and comply with the National Minimum Care Standards. All machines feature a large door opening, making them ideal for bulky items and duvets.

Suitable for OTEX Validated Disinfection System.

Features

Built-in Type 'A' air gap
 Microprocessor controlled
 Information display
 Free-standing
 Two spin speeds
 Two sluice programmes
 High build quality
 Liquid soap injection control board
 Large door opening

Benefits

Eliminates the risk of water contamination and fully approved for direct connection to mains water, resulting in lower installation costs.
 Standard with customised wash cycles to suit individual needs.
 Displays cycle selected, operating temperature, minutes remaining until the end of cycle enabling more efficient use of staff time.
 Lower installation cost. No bolting down required.
 1,000rpm super spin, reduces drying time by up to 30% - saves cost, increases throughput and eliminates need for separate hydro extractor. Standard spin speed for delicates prevents creasing and fabric damage.
 Separate programmes for both thermal and chemical disinfection depending on type of fabric being processed. Enables all laundry including heat labile fabrics to be processed without handling foul or infected items.
 Stainless steel cabinet and drum - clean and hygienic, robust and reliable.
 Easy connection to auto-dosing pump system.
 Ideal for duvets and bulky items.

For further information call 0800 591903

JLA Limited Meadowcroft Lane, Ripponden, West Yorkshire HX6 4AJ

T 01422 822282 **F** 01422 824390 **email** info@jla.com

JLA Limited River Lodge, Lucan, County Dublin **T** 01 601 0525 **F** 01 628 1937



Working harder to reduce your carbon footprint

www.jla.com